

KANON**Minimal torque gauge, maximum torque: 150cNm****Order data**

Order number	658800 150
GTIN	4582126965471
Item class	66F

Description**Version:**

Accurate measuring instrument for the smallest torques. Easy-to-read scale with memory pointer on the top and additional scale on the side. **With 3-jaw steel chuck.**

Application:

For measuring the smallest torques (such as rotation and frictional resistances) and for controlled tightening of screws.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Clamping chuck range	1 - 8.5 mm
Weight	600 g
maximum torque	150 cNm
Ø	63 mm
Torque range	10 - 150 cNm
Torque range	100 - 1500 mNm
Release signalling	visual
Setting the trigger value	Memory pointer

Series	SGK
Adjustable trigger value	non-adjustable
Measurement process	Torque
Display	analogue
Scale graduation, 1 graduation =	2 cNm
Overall length L	132 mm
Feedback	displaying
Connection format	3-jaw chuck
Standard	DIN EN ISO 6789
Reversible reading	Nm
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Torque measuring accuracy	±3 %
Data can be recorded	no
Measurement technology	mechanical
Type of product	Torque Wrench

Services

CalibrationTorque wrench clockwise / anti-clockwise
maximum torque 400/2 N·m

020030 400/2