



## GARANT Power Tang 90° tangential high-performance indexable end mill, Weldon shank, Ø D / Zeff: 25/2\_ mm

### Order data

Order number	215972 25/2_
GTIN	4045197939746
Item class	210

### Description

Power Tang 90° high performance tangential end mill 25/2\_ mm number of effective inserts  $n_{eff}$ : 2  
 Number of inserts: 10  
 maximum cutting depth  $a_{p,max}$ : 39 mm  
 Overhang  $L_1$ : 54 mm  
 Overall length  $L_{tot}$ : 112 mm  
 Shank Ø  $D_s$  h6: 25 mm

### Technical description

Spacing of the cutters	unequal spacing
Tool exchange	PowerCard
Machining strategy	
Setting angle $\kappa$	90 degrees
Through-coolant	yes
Shank type	Weldon shank
Milling application	Corner milling
Norm	
Type of product	