

**HOLEX®**
**Welder's clamp, overall length: 275 mm**

**Order data**

Order number	709200 275
GTIN	4045197896056
Item class	76B

**Description**
**Version:**

U-shaped clamping jaws; upper jaw angled 90°. Sturdy spring steel body. Fully nickel-plated.

**Application:**

For clamping profiled or flat materials etc. when welding.

**Material:**

Chrome vanadium steel clamping jaws.

**Spare part:**

Spare spring No. 708301 size 10.

Jaw capacity a: 55 mm

**Technical description**

overall length	275 mm
Jaw capacity a	55 mm
upper gripper jaw	90° angled
Type of jaws	U-shape
Material of pliers	Spring steel
Material of gripper jaws	Chrome vanadium steel
Surface	nickel-plated

