

Garant

GARANT Power Tang 90° tangential high-performance shoulder mill wide pitch, Weldon shank, Ø D / number of effective cutting edges Z: 25/3mm



Order data

Order number	215950 25/3
GTIN	4045197939814
Item class	210

Description

Version:

Maximum stability due to tangentially arranged inserts.

High feed rate values for maximum metal removal rate due to optimum indexable insert with stability in the direction of the cutting force.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

Technical description

Number of cutting edges Z	3
Overhang L_1	30 mm
Shank $\varnothing D_s$ h6	25 mm
Overall length L_{tot}	105 mm
suitable indexable insert	LO.U0904..
maximum cutting depth $a_{p,max}$	8 mm
Cutting edge $\varnothing D_c$	25 mm
Pack of insert screws	219868 2 (8IP; 1.2 Nm)
Series	Power Tang
Shank type	Weldon shank
Setting angle κ	90 degrees

Milling application	Corner milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2