

Garant**Torque screwdriver with scale, to take D 6.3 bits, maximum torque: 50cNm****Order data**

Order number	659905 50
GTIN	4045197610997
Item class	61E

Description**Version:**

Power grip with comfortable easy-grip **Haptoprene®** surface allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection). The desired torque is set using an adjustment wheel at the end of the handle. Putting the wheel into the locked position prevents inadvertent changes to the setting. Easy to read micrometer scale, protected against dirt.

Bit holder with magnet to take C 6.3 bits.

Standard:

Tested to DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Scale graduation, 1 graduation =	1 cNm
maximum torque	50 cNm
Display	analogue
Torque measuring accuracy	±6 %
Bit socket	D 6,3
Torque range	10 - 50 cNm

Data sheet

Torque range	0.1 - 0.5 Nm
Measurement process	Torque
Standard	DIN EN ISO 6789
Weight	71 g
Trigger principle	mechanical slip clutch
Setting the trigger value	with adjustment scale
Reversible reading	cNm
Overall length L	126 mm
Adjustable trigger value	adjustable
Connection format	Bit holder 1/4 inch
Feedback	triggering
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
maximum Ø	29 mm
Torque fixed setting	no
Type of product	Torque screwdriver

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/659905-50>