



## Torque screwdriver with scale, maximum torque: 880cNm



### Order data

Order number	659933 880
GTIN	4013288119308
Item class	63F

### Description

#### Version:

**Kraftform** handle for easy transmission of the required torque. With **Rapidaptor** quick-change holder for 1/4 inch bits with C 6.3 **and** E 6.3 shank.

Torque setting by hand using a micrometer scale (from size 600 using the integral auxiliary tool or a 17AF open spanner). With pistol grip for delivering high torques.

#### Function:

When the set torque is reached the screwdriver triggers, with clearly audible and perceptible signals. The triggering torque is unrestricted.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Rapidaptor free-running coupling shank available from our eShop (No. 675035 size 6.3F).

### Technical description

Scale graduation, 1 graduation =	40 cNm
Display	analogue
maximum torque	880 cNm

Torque measuring accuracy	±6 %
Bit socket	F 6.3
Bit socket	D 6,3
Torque range	400 - 880 cNm
Torque range	4 - 8.8 Nm
Connection format	Bit holder 1/4 inch
Reversible reading	cNm
Adjustable trigger value	adjustable
Trigger principle	mechanical short-travel release
Feedback	triggering
Standard	DIN EN ISO 6789
Measurement process	Torque
Setting the trigger value	with adjustment scale
Weight	278 g
Overall length L	150 mm
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Manufacturer's designation	7400 pistol
Type of product	Torque screwdriver

## Services

Calibration Torque screwdriver maximum torque 0,04-20 N·m

020200 0,04-20

