

Swarf container with perforated intermediate floor, Skip volume: 750l



Order data

Order number	919930 750
GTIN	2050001936769
Item class	94B

Description

Version:

The bucket is oil-tight and watertight. It is fitted with a **bolted-on perforated plate over the entire base** and with a 1 inch discharge valve. Therefore it is **particularly well suited for collecting and separating liquids from solids**.

The container has a wall thickness of 3 mm. Tipping it can easily be activated by cable from the truck driver's seat.

The base frame includes sockets for fork-lift forks.

With protection against accidental slippage. The sheet steel body of the container has a strengthening profile around the edge.

Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, reseda green RAL 6011, mouse grey RAL 7005.

Technical description

Height	680 mm
Filling edge height	495 mm
Drain cock version	Delivery tap without sieve

with fork insertion slots	yes
Internal dimension at intake: width	200 mm
Skip volume	750 l
Safe working load	1000 kg
Tipping mechanism	Pull cord
Width	1280 mm
Pull cord	yes
Internal dimension at intake: height	60 mm
Fork insertion slots dimension D	60 mm
Weight	169 kg
Fork insertion slots dimension A	200 mm
welded oil-tight	yes
Length	1440 mm
Fork-lift fork socket pitch B	495 mm
Perforated panel fittings	Perforated shelf
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers

Accessories

Set of wheels for tilting containers and swarf containers, polyamide, 4 pieces Load capacity / wheel 450 kg

919970 450