



Torque screwdriver with scale, maximum torque: 250cNm



Order data

Order number	659936 250
GTIN	3148516660640
Item class	63V

Description

Version:

Robust torque screwdriver, adjustable with parallax-free micrometer scale. 1/4 inch internal square at the end of the handle.

Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

maximum torque	250 cNm
Display	analogue
Scale graduation, 1 graduation =	10 cNm
Torque measuring accuracy	±6 %
Bit socket	D 6,3
Torque range	50 - 250 cNm
Torque range	0.5 - 2.5 Nm
Overall length L	147 mm
Standard	ISO 6789

Reversible reading	Nm
Weight	280 g
Setting the trigger value	with adjustment scale
Measurement process	Torque
Trigger principle	mechanical slip clutch
Adjustable trigger value	adjustable
Connection format	Bit holder 1/4 inch
Feedback	triggering
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	acoustic
Measurement technology	mechanical
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------

Accessories

Handle with reversible ratchet	659937
--------------------------------	--------