

**Tipper truck RAL 7035 with discharge valve, Skip volume: 250l****Order data**

Order number	919922 250
GTIN	4017976847016
Item class	96D

**Description****Version:**

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and protection against overturning.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

**Callout:**

Discharge valve

with sieve for separating liquids from solids.

Tipping action is operated manually.

For emptying using a forklift truck or when heavily loaded we recommend a self-tipper.

**Standard:**

**EN 1757-3**

**Colour:**

Light grey RAL 7035 **powder-coated.**

**Technical description**

Number of castors with parking brake	2
Width	713 mm

Height	780 mm
Number of wheels	4
Fork insertion slots dimension D	72 mm
Pull cord	no
Skip volume	250 l
Bucket height	413 mm
with fork insertion slots	yes
welded oil-tight	yes
Tipping mechanism	manual
Drain cock version	Delivery tap with sieve
Tipping prevention	yes
Weight	70 kg
Length	1359 mm
Fork-lift fork socket pitch B	203 mm
Material of wheel	TPE
Fork insertion slots dimension A	194 mm
Wheel Ø	200 mm
Fork insertion slots dimension C	603 mm
Internal dimension at intake: height	72 mm
Number of fixed wheels without parking brake	2
Safe working load	750 kg
Filling edge height with rollers	780 mm
Bucket width	652 mm
Internal dimension at intake: width	194 mm
Bucket length	1200 mm
Colour	light grey RAL 7035
Standard	EN 1757-3
Type of product	Tilting containers

