



## Torque screwdriver with scale, maximum torque: 1000cNm



### Order data

Order number	659936 1000
GTIN	3148516660480
Item class	63V

### Description

#### Version:

Robust torque screwdriver, adjustable with parallax-free micrometer scale. 1/4 inch internal square at the end of the handle.

#### Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

### Technical description

Display	analogue
Scale graduation, 1 graduation =	50 cNm
maximum torque	1000 cNm
Torque measuring accuracy	±6 %
Bit socket	D 6,3
Torque range	200 - 1000 cNm
Torque range	2 - 10 Nm
Trigger principle	mechanical slip clutch
Setting the trigger value	with adjustment scale

Connection format	Bit holder 1/4 inch
Adjustable trigger value	adjustable
Feedback	triggering
Standard	ISO 6789
Overall length L	168 mm
Reversible reading	Nm
Measurement process	Torque
Weight	400 g
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	acoustic
Measurement technology	mechanical
Type of product	Torque screwdriver

## Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------

## Accessories

Handle with reversible ratchet	659937
--------------------------------	--------