

Tilting container with roller system, painted, Skip volume: 300l



Order data

Order number	919950 300
GTIN	2050001936790
Item class	94B

Description

Version:

Tilting container **for solid materials** with a well-balanced centre of gravity. A pull cable allows the container to be tipped at any height.

The sheet steel body of the container has a strengthening profile around the edge and a sturdy base frame with slots for fork-lift forks. A catch prevents accidental slipping off or tipping.

Fork-lift slots internal dimensions A×D = 200×80 mm.

Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, reseda green RAL 6011, mouse grey RAL 7005.

Technical description

Weight	112 kg
Tipping prevention	yes
with pull cord	yes
Height	835 mm
Safe working load	750 kg

Width	770 mm
Fork-lift fork socket pitch B	300 mm
Length	1260 mm
Application range	for solids
Skip volume	300 l
Filling edge height	740 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers

Accessories

Set of wheels for tilting containers and swarf containers,
polyamide, 4 pieces Load capacity / wheel 450 kg

919970 450