



## Torque screwdriver without scale, maximum torque: 300cNm



### Order data

Order number	659934 300
GTIN	4013288102928
Item class	63F

### Description

#### Version:

**Kraftform** handle for easy transmission of the required torque. With **Rapidaptor** quick-change holder for 1/4 inch bits with C 6.3 **and** E 6.3 shank.

The torque can be set using a torque analyser (No. 654300 – 654460) and a 7AF hexagon screwdriver (10AF for size 600) . **The torque screwdrivers are factory-set to the most frequently used torque setting.**

#### Function:

When the set torque is reached the screwdriver triggers, with clearly audible and perceptible signals. The triggering torque is unrestricted.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Rapidaptor free-running coupling shank available from our eShop (No. 675035 size 6.3F).

### Technical description

set torque	1.2 Nm
1 turn (360°) corresponds to	20 cNm
maximum torque	300 cNm
Torque measuring accuracy	±6 %
Bit socket	D 6,3

Bit socket	F 6.3
Torque range	120 - 300 cNm
Torque range	1.2 - 3 Nm
Feedback	triggering
Standard	DIN EN ISO 6789
Overall length L	155 mm
Connection format	Bit holder 1/4 inch
Reversible reading	cNm
Adjustable trigger value	preset
Setting the trigger value	without setting scale (requires torque analyser)
Trigger principle	mechanical short-travel release
Weight	180 g
Measurement process	Torque
Calibration	O6
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Manufacturer's designation	7400 pre-set, 105 mm
Type of product	Torque screwdriver

## Services

Calibration and adjustment Torque screwdriver without scale maximum torque 0,04-20 N·m

020170 0,04-20

## Accessories

Electronic torque screwdriver tester "TST" maximum torque  
10 N·m

---

654300 10