



Torque screwdriver without scale, maximum torque: 600cNm



Order data

Order number	659934 600
GTIN	4013288102935
Item class	63F

Description

Version:

Kraftform handle for easy transmission of the required torque. With **Rapidaptor** quick-change holder for 1/4 inch bits with C 6.3 and E 6.3 shank.

The torque can be set using a torque analyser (No. 654300 – 654460) and a 7AF hexagon screwdriver (10AF for size 600) . **The torque screwdrivers are factory-set to the most frequently used torque setting.** With pistol grip for delivering high torques.

Function:

When the set torque is reached the screwdriver triggers, with clearly audible and perceptible signals. The triggering torque is unrestricted.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Rapidaptor free-running coupling shank available from our eShop (No. 675035 size 6.3F).

Technical description

set torque	3 Nm
maximum torque	600 cNm
1 turn (360°) corresponds to	50 cNm

Torque measuring accuracy	±6 %
Bit socket	F 6.3
Bit socket	D 6,3
Torque range	300 - 600 cNm
Torque range	3 - 6 Nm
Feedback	triggering
Adjustable trigger value	preset
Trigger principle	mechanical short-travel release
Overall length L	150 mm
Weight	266 g
Standard	DIN EN ISO 6789
Setting the trigger value	without setting scale (requires torque analyser)
Connection format	Bit holder 1/4 inch
Reversible reading	cNm
Measurement process	Torque
Calibration	O6
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Manufacturer's designation	7400 pre-set, pistol handle
Type of product	Torque screwdriver

Services

Calibration and adjustment Torque screwdriver without scale maximum torque 0,04-20 N·m

020170 0,04-20

Accessories

Electronic torque screwdriver tester "TST" maximum torque
10 N·m

654300 10