



## Self-tipping truck with discharge valve, Skip volume: 350l



### Order data

Order number	919925 350
GTIN	4017976160306
Item class	96D

### Description

#### Version:

Sturdy welded construction of 3 mm sheet steel. Chassis with integral fork lift slots.  
2 fixed wheels and 2 castors (with parking brake) with nylon tyres.  
Roll restraint and tip position locking, chain acts as protection against slipping off and tipping.

#### Callout:

**Discharge valve** with sieve for separating liquids from solids.

**Tipping action is performed automatically when the interlock is released.**

Pull cord to initiate tipping from the forklift seat position.

#### Standard:

**EN 1757-3**

#### Colour:

Brilliant blue RAL 5007 **powder-coated**.

### Technical description

Pull cord	yes
Tipping mechanism	Pull cord
Fork-lift fork socket pitch B	192 mm
Number of wheels	4

Fork insertion slots dimension C	592 mm
Drain cock version	Delivery tap with sieve
with fork insertion slots	yes
Skip volume	350 l
Number of fixed wheels without parking brake	2
Height	1070 mm
Fork insertion slots dimension A	190 mm
Fork insertion slots dimension D	90 mm
Internal dimension at intake: height	90 mm
Material of wheel	Polyamide
Length	1294 mm
Filling edge height with rollers	981 mm
Safe working load	1000 kg
Internal dimension at intake: width	190 mm
Weight	126 kg
Width	731 mm
Wheel Ø	200 mm
Number of castors with parking brake	2
Tipping prevention	yes
Colour	brilliant blue RAL 5007
Standard	EN 1757-3
Height without rollers	837 mm
Type of product	Tilting containers