



## Torque screwdriver with scale, maximum torque: 300cNm



### Order data

|              |               |
|--------------|---------------|
| Order number | 659945 300    |
| GTIN         | 4045197514011 |
| Item class   | 62E           |

### Description

#### Version:

Practical handle for transmission of the required torques without problems. Easy to read micrometer scale, protected against dirt. Lock at the end of the handle against inadvertent adjustment. Interchangeable blade to take 1/4 inch bits included.

#### Function:

On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use.

#### Application:

For controlled tightening of screws to a pre-set torque.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

All Wiha interchangeable blades (No. 659940 – 659946) can also be used in the Holey torque screwdriver No. 659945.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

### Technical description

|                                  |          |
|----------------------------------|----------|
| maximum torque                   | 300 cNm  |
| Display                          | analogue |
| Scale graduation, 1 graduation = | 10 cNm   |
| Torque measuring accuracy        | ±6 %     |
| Bit socket                       | D 6,3    |

|                           |                                     |
|---------------------------|-------------------------------------|
| Torque range              | 60 - 300 cNm                        |
| Torque range              | 0.6 - 3 Nm                          |
| Overall length L          | 153 mm                              |
| Weight                    | 300 g                               |
| Setting the trigger value | with adjustment scale               |
| Reversible reading        | cNm                                 |
| Reversible reading        | Nm                                  |
| Connection format         | Bit holder 1/4 inch                 |
| Feedback                  | triggering                          |
| Measurement process       | Torque                              |
| Standard                  | DIN EN ISO 6789                     |
| Trigger principle         | mechanical slip clutch              |
| Adjustable trigger value  | adjustable                          |
| Calibration               | O1                                  |
| Direction of tightening   | For right- and left-hand tightening |
| Test certificate          | Manufacturer's test certificate     |
| Data can be recorded      | no                                  |
| Release signalling        | acoustic                            |
| Release signalling        | haptisk                             |
| Measurement technology    | mechanical                          |
| Type of product           | Torque screwdriver                  |

## Services

|  |                |
|--|----------------|
| CalibrationTorque screwdriver maximum torque 0,04-20 N·m | 020200 0,04-20 |
|--|----------------|

## Accessories

|  |          |
|--|----------|
| Torque interchangeable bladefor Phillips Cross-head size 1 | 659940 1 |
| Torque interchangeable bladePozidriv Cross-head size 1     | 659941 1 |

|   |          |
|---|----------|
| Torque interchangeable blade for Phillips Cross-head size 0 | 659940 0 |
| Interchangeable blade 1/4 inch                              | 659947   |
| Torque interchangeable blade Pozidriv Cross-head size 0     | 659941 0 |