

Tilting container with roller system, painted, Skip volume: 900l



Order data

Order number	919950 900
GTIN	2050001937414
Item class	94B

Description

Version:

Tilting container **for solid materials** with a well-balanced centre of gravity. A pull cable allows the container to be tipped at any height.

The sheet steel body of the container has a strengthening profile around the edge and a sturdy base frame with slots for fork-lift forks. A catch prevents accidental slipping off or tipping.

Fork-lift slots internal dimensions AxD = 200x80 mm.

Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, reseda green RAL 6011, mouse grey RAL 7005.

Technical description

Skip volume	900 l
Length	1260 mm
Application range	for solids
Width	1570 mm
Height	835 mm

Tipping prevention	yes
with pull cord	yes
Fork-lift fork socket pitch B	600 mm
Weight	165 kg
Safe working load	1000 kg
Filling edge height	740 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers

Accessories

Set of wheels for tilting containers and swarf containers,
polyamide, 4 pieces Load capacity / wheel 450 kg

919970 450