

**Self-tipping truck with discharge valve, Skip volume: 900l****Order data**

Order number	919925 900
GTIN	4017976160900
Item class	96D

**Description****Version:**

Sturdy welded construction of 3 mm sheet steel. Chassis with integral fork lift slots.  
2 fixed wheels and 2 castors (with parking brake) with nylon tyres.  
Roll restraint and tip position locking, chain acts as protection against slipping off and tipping.

**Callout:**

**Discharge valve** with sieve for separating liquids from solids.

**Tipping action is performed automatically when the interlock is released.**

Pull cord to initiate tipping from the forklift seat position.

**Standard:**

**EN 1757-3**

**Colour:**

Brilliant blue RAL 5007 **powder-coated.**

**Technical description**

Skip volume	900 l
Safe working load	2000 kg
Fork insertion slots dimension C	982 mm
Height	1078 mm

Material of wheel	Polyamide
Internal dimension at intake: width	190 mm
Fork-lift fork socket pitch B	582 mm
Number of fixed wheels without parking brake	2
Weight	184 kg
Tipping prevention	yes
Tipping mechanism	Pull cord
Drain cock version	Delivery tap with sieve
Filling edge height with rollers	989 mm
Number of castors with parking brake	2
Fork insertion slots dimension D	90 mm
Number of wheels	4
with fork insertion slots	yes
Fork insertion slots dimension A	190 mm
Width	1661 mm
Internal dimension at intake: height	90 mm
Wheel Ø	200 mm
Pull cord	yes
Length	1294 mm
Colour	brilliant blue RAL 5007
Standard	EN 1757-3
Height without rollers	837 mm
Type of product	Tilting containers