



## Pneumatic-hydraulic pop rivet tool TAURUS®, Type: 3



### Order data

Order number	770512 3
GTIN	4007081580007
Item class	74A

### Description

**Version:**

Operating pressure 5 – 7 bar. Removable rivet pin capture box.

**Advantage:**

The **gripping jaw system** ensures very long tool life and a non-slip grip on the rivet spigot. Low compressed air consumption due to two-phase operation: for setting **and** for lifting away the broken-off tail. Very quick operating cycle.

**Supplied with:**

Assembly spanners 12 / 14 AF and 14 / 17 AF.

1 bottle hydraulic oil 100 ml and 1 oil refill container. Including nozzles 17/ 36, 17/ 40, 17/ 45.

### Technical description

Tool stroke	25 mm
for pop rivets steel / aluminium up to	6.4 mm
Hose connection	6 mm
Air consumption per rivet	4.8 l
Setting force at 5 bar	14000 N

Weight	1.9 kg
maximum mandrel Ø	4.5 mm
for pop rivets in all materials up to	6.4 mm
Hose connection	1/4 in
Type of product	Pop riveter