



ECO knurl forming tool universal, Shank size: 8 mm



Order data

Order number	290035 8
GTIN	4030741290657
Item class	29I

Description

Version:

Used conventionally.

Note:

Tip height must be adjusted.

for knurl profile: RGV30° 1×GE30°

for knurl $\varnothing d_1$: 15 mm

for knurl width w: 4 mm

for knurl bore $\varnothing d_2$: 4 mm

Working range: 3 - 20 mm

Roller pin: 299911 2

Technical description

Roller pin	299911 2
Shank width	8 mm
Shank height	8 mm
for knurl bore $\varnothing d_2$	4 mm
Working range	3 - 20 mm
for knurl width w	4 mm
for knurl $\varnothing d_1$	15 mm
Cutting direction	left-hand and right-hand
for knurl profile	RGE30° 1×GV30°

for knurl profile	RBR 1×BL
for knurl profile	RAA 1×AA
for knurl profile	RBL 1×BR
for knurl profile	RGV30° 1×GE30°
Type of product	Self-centering knurling tool