

Garant**Arbor for screw-in milling cutters with thread, SK 40, Thread M×length L1:
M10X231****Order data**

Order number	301313 M10X231
GTIN	4045197942821
Item class	31A

Description**Version:**

Vibration damped version, arbor with vibration-damping core.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Technical description

External Ø D	41 mm
Thread M	M10×231
Reach L ₁	231 mm
Bore Ø D ₁	10.5 mm
Overhang dimension A	250 mm
Ø D ₂	18 mm
L ₂	7 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor