

Garant

Arbor for screw-in milling cutters with thread vibration-damped, tapered form, HSK-A 63, Thread M×length L1: M10X224



Order data

Order number	307038 M10X224
GTIN	4045197942890
Item class	31A

Description

Version:

With RFID/Balluffchip bore. Tapered design. **Vibration damped version, arbor with vibration-damping core.**

Application:

To take screw-in milling cutters with thread.

Optional extras:

Extensions No. 301342, reducers No. 301344, coolant tube No. 309880, coolant tube socket wrench No. 309890.

Note:

Densimet arbors and solid carbide extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

Overhang dimension A: 250 mm

Bore $\varnothing D_1$: 10.5 mm

$\varnothing D_2$: 18 mm

External $\varnothing D$: 40 mm

Reach L_1 : 224 mm

L_2 : 5 mm

Technical description

External $\varnothing D$	40 mm
$\varnothing D_2$	18 mm

Overhang dimension A	250 mm
L ₂	5 mm
Thread M	M10×224
Bore Ø D ₁	10.5 mm
Reach L ₁	224 mm
Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor