

Garant**Arbor for screw-in milling cutters with thread, SK 40, Thread M×length L1:
M12X231****Order data**

Order number	301313 M12X231
GTIN	4045197942845
Item class	31A

Description**Version:**

Vibration damped version, arbor with vibration-damping core.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Technical description

Bore $\varnothing D_1$	12.5 mm
L_2	7.5 mm
Overhang dimension A	250 mm
$\varnothing D_2$	21 mm
Thread M	M12×231
Reach L_1	231 mm
External $\varnothing D$	44 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor