

Garant
eco screw-on toolholder, right-hand, Shank size / insert size: 16/09mm


Order data

Order number	260020 16/09
GTIN	4045197945150
Item class	21U

Description

Version:

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability. With flank face cooling.

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Through-coolant: yes

ISO code toolholder: SCLCR/L 1616X09

suitable indexable insert: CC.. 09T3..

Functional width L₄: 20 mm

Head length L₁: 27 mm

Overall length L: 74 mm

Pack of insert screws: 269028 28

Technical description

Head length L ₁	27 mm
ISO code toolholder	SCLCR/L 1616X09
Functional width L ₄	20 mm
Insert size	9 mm
Pack of insert screws	269028 28

suitable indexable insert	CC.. 09T3..
Overall length L	74 mm
Shank size	16 mm
Series	Eco
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	95 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15