

**Garant****eco screw-on toolholder, right-hand, Shank size / insert size: 20/11 mm**

## Order data

Order number	261304 20/11
GTIN	
Item class	21U

## Description

### Version:

GARANT eco system screw-on toolholder with internal coolant feed to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability. With flank face cooling.

### Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No.317900 – 319886.

## Technical description

Insert size	11 mm
Head length L <sub>1</sub>	40 mm
Pack of insert screws	269023 1
Overall length L	99 mm
Functional width L <sub>4</sub>	25 mm
Shank size	20 mm
suitable indexable insert	VC.. 1103..
ISO code toolholder	SVJCR/L 2020X11
Series	Eco
Application type	right-hand

Standard	DIN ISO 5610
Through-coolant	yes
Setting angle $\kappa$	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8