

Garant
eco screw-on toolholder, left-hand, Shank size / insert size: 20/11 mm

Order data

Order number	261103 20/11
GTIN	4045197945280
Item class	21U

Description
Version:

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

With flank face cooling.

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Through-coolant: yes

ISO code toolholder: SVJBR/L 2020X11

suitable indexable insert: VB.. 1103..

Functional width L_4 : 25 mm

Head length L_1 : 40 mm

Overall length L: 99 mm

Pack of insert screws: 269023 1

Technical description

Shank size	20 mm
suitable indexable insert	VB.. 1103..
Head length L_1	40 mm
ISO code toolholder	SVJBR/L 2020X11
Functional width L_4	25 mm

Pack of insert screws	269023 1
Overall length L	99 mm
Insert size	11 mm
Series	Eco
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8