

Garant
eco screw-on toolholder, left-hand, Shank size / insert size: 20/16mm

Order data

Order number	261103 20/16
GTIN	
Item class	21U

Description
Version:

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

With flank face cooling.

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Technical description

ISO code toolholder	SVJBR/L 2020X16
Shim screw	269013 1
Head length L ₁	40 mm
Shank size	20 mm
Pack of insert screws	269023 3
suitable indexable insert	VB.. 1604..
Overall length L	99 mm
Insert size	16 mm
Shim	259033 5
Series	Eco

Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15