

Garant
ER collet chuck Form ADB, nickel plated, SK 40 A = 70, for ER collet size: 40

Order data

Order number	300515 40
GTIN	4045197945846
Item class	31A

Description
Version:

Taper ground internally and externally. With Balluffchip bore.

GARANT –

- **very smooth running due to hard turned shanks precision balanced to G2.5 / 25000 rpm.**
- **optimum corrosion protection due to nickel-plated surfaces.**
- **very high clamping forces and accuracy thanks to GARANT precision clamping nuts.**

Special nickel plating.

GARANT –

- **Balancing quality G2.5 / 25,000 rpm**
- **All shanks hard turned (for smooth running!).**
- **GARANT precision clamping nut, fine balanced (G 2.5 / 25,000 rpm) and coated, giving high clamping force and low wear.**
- **Through bored.**

Application:

For clamping tools with plain shank in collets to DIN 6499 – Form A and B.

Supplied with:

Clamping nut.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS pull stud wrenches No.308820 – 308835, ER chuck key No. 309680 – 613300, ER collets No. 308901 – 309449, ER clamping nuts No. 309615 (for sealing rings), sealing rings No. 309625 – 309645 (for No. 309615).

Machining strategy: HSC

Clamping range: 3 - 26 mm

External Ø D: 63 mm

Spare GARANT high-speed clamping nut No. 309610: 40

Spare HOLEX nut No. 309580: 40

Technical description

Clamping range	3 - 26 mm
for ER collets	40
External Ø D	63 mm
Spare GARANT high-speed clamping nut No. 309610	40
Spare HOLEX nut No. 309580	40
Adapter	SK 40 A = 70
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

Accessories

ER chuck key for ER collet chuck 40	309680 40
-------------------------------------	-----------