


## Groove width gauge with numerical tolerance, Type: C



### Order data

Order number	484411 C
GTIN	2050001956712
Item class	48B

### Description

#### Version:

For intermediate sizes or numerical tolerances.

Groove width gauges with "Go" and "No Go" end. "Go" end with **wear allowance** to DIN 7164.

Gauge body of hardened steel.

Groove width gauge with numerical tolerance, e.g. 484411 Gr. **41.04 +0.01/-0.02**.

#### Application:

For checking flat fits, e.g. grooves.

#### Standard:

Toleranzen und Abmaße nach **DIN 1938-1 und DIN 7164**.

#### Note:

The size designation type describes the nominal dimension in millimetres (mm).

Type A = 3.001 – 5.999

Type B = 6.001 – 8.999

Type C = 9.001 – 12.999

Type D = 13.001 – 16.999

Type E = 17.001 – 20.999

Type F = 21.001 – 25.999

### Technical description

Nominal size	9.001 - 12.999 mm
Tolerance value	-2.7 mm
Standard	DIN 7164

Standard	DIN 1938-1
Tolerance zone	G
Tolerance zone	A
Tolerance zone	B
Tolerance zone	C
Tolerance zone	CD
Tolerance zone	D
Tolerance zone	E
Tolerance zone	EF
Tolerance zone	F
Tolerance zone	FG
Tolerance zone	J
Tolerance zone	H
Tolerance zone	JS
Tolerance zone	K
Tolerance zone	M
Tolerance zone	P
Tolerance zone	N
Tolerance zone	R
Tolerance zone	S
Tolerance zone	U
Tolerance zone	T
Tolerance zone	V
Tolerance zone	X
Tolerance zone	ZC
Tolerance zone	ZA
Tolerance zone	Z
Tolerance zone	ZB
Tolerance zone	ZC

Quality	7
Quality	8
Quality	9
Quality	10
Quality	11
Quality	12
Quality	13
Calibration	L6
Type of product	Shaft slot gauge

## Services

Calibration "Go" / "No Go" plug gauge maximum Ø 20 mm	028300 20
---	-----------