

**Garant**
**Hand reamer Configurable, uncoated, Nominal Ø DC: 12mm**

**Order data**

Order number	160200 12
GTIN	4045197927057
Item class	10N

**Description**
**Version:**

With **left-hand helix** 7 – 8° and long taper lead, more than 1/4 of the cutting length. An even number of teeth with irregular spacing for accurately round holes, free of chatter. The cylindrical ground chamfer on the plain cutting section smooths the hole and guides the reamer.

Hand reamers **finish ground to match your specifications.**

**Application:**

For through holes (not for blind holes). Also very suitable for interrupted holes.

**Technical description**

Nominal Ø D <sub>c</sub>	12 mm
Overall length L	152 mm
Ø range	11.601 - 12.3 mm
Shank square □	9 mm
Flute length L <sub>c</sub>	76 mm
Number of cutting edges Z	6
Overhang L <sub>1</sub>	97 mm
Coating	uncoated
Tool material	HSS
Standard	DIN 206 B
Helix angle	7-8 degrees
Through-coolant	no

Application for type of drilling	for through holes
Colour ring	without
Type of product	Phillips bit

**User data**

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions		
Oil	suitable		
dry	suitable only under restricted conditions		