

Garant

Toolholder for VDI profile broaching tools $\varnothing d = 12$ mm, Shank mounting type: VDI25

**Order data**

Order number	293030 VDI25
GTIN	4045197946140
Item class	29K

Description**Suitable for:**

CNC machines.

Optional extras:

Positioning aid (No. 293000) and pin wrench (No. 293006).

Note:

- **Caution: Always use appropriate slotting tool \varnothing .**
- **Other shank connections on request.**

Technical description

L	64 mm
$\varnothing D_2$	58 mm
$\varnothing D_1$	44 mm
Shank type	VDI 25
$\varnothing d$	12 mm

Arbor size	VDI25
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool

Accessories

Pin spanner for holder Ø 5 mm	293006 5
Pin spanner for holder Ø 16 mm	293006 16
Pin spanner for holder Ø 8 mm	293006 8
Pin spanner for holder Ø 12 mm	293006 12