

Garant

High-Performance face mill arbor vibration-damped, cylindrical with cooling channel bores, SK 50 A = 200, Spigot Ø d1: 16mm



Order data

Order number	301103 16
GTIN	4045197946096
Item class	31H

Description

Version:

- **Taper shank, spigot, and all contact surfaces are ground at the collar.**
- **With RFID / Balluffchip bore.**
- **Larger collar contact face.**

Advantage:

The heavy metal core specially matched to the arbors gives optimum machining results even with long overhangs:

- **Saves time, because allows use of the maximum machining parameters.**
- **Smooth running and thus perfect surface quality results.**
- **Saves costs, because tool life is increased.**
- **Less vibrational stress on the machine headstock.**

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Note:

Balance quality G 6.3 dependent on the maximum operating speed.
Further sizes on request.

Technical description

Overhang dimension A	200 mm
Milling mandrel length L ₄	17 mm
Spigot Ø d ₁	16 mm

Data sheet

maximum speed $n_{\max}$	8000 min ⁻¹
External Ø D	38 mm
Clamping Ø D ₁	16 mm
Adapter	SK 50 A = 200
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	AD
Cooling channel bore	lockable
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Vibration	damped
Through-coolant	yes
Type of product	Milling head arbor