

 **HALDER****Centring clamping element with clamping segments, Type: 2****Order data**

Order number	370017 2
GTIN	4030618238737
Item class	37K

**Description****Advantage:**

- **Precise self-centring with an accuracy of  $\pm 0.025$  mm.**
- **The clamping elements allow components with rough or machined surfaces to be positively centred and pulled down at the seating point.**
- **Large adjustment range even at low overall height.**
- **Can be bolted on from above or below.**

**Application:**

For centring and clamping components with a location bore.

**Material:**

Base of tool steel, hardened, burnished. Clamping elements of stainless steel 1.4112, hardened and ground.

**Technical description**

$D_{\min}$	18.5 mm
$h_2$	11.6 mm
$D_{\max}$	22.5 mm
Clamping force	4.5 kN

$\varnothing d_4$	M5 mm
$h_4$	7.5 mm
$d_3 f7$	15 mm
$h_5$	23.6 mm
Type of product	Jig clamping system