

HALDER**Centring clamping element with clamping balls, Type: 5****Order data**

Order number	370018 5
GTIN	4030618238935
Item class	37K

Description**Advantage:**

- **Precise self-centring with an accuracy of ± 0.025 mm.**
- **The clamping elements allow components with rough or machined surfaces to be positively centred and pulled down at the seating point.**
- **Large adjustment range even at low overall height.**
- **Can be bolted on from above or below.**

Application:

For centring and clamping components with a location bore.

Material:

Base of tool steel, hardened, burnished. Clamping elements of stainless steel 1.4112, hardened and ground.

D_{\min} : 30.5 mm

D_{\max} : 38.5 mm

d_3 f7: 25 mm

$\varnothing d_4$: M6 mm

h_2 : 15.2 mm

h_4 : 7 mm

Technical description

D_{\min}	30.5 mm
D_{\max}	38.5 mm
h_4	7 mm
Clamping force	5 kN
$\varnothing d_4$	M6 mm
h_2	15.2 mm
$d_3 f7$	25 mm
h_5	33.4 mm
Type of product	Jig clamping system