

**Garant**
**Face mill arbor cylindrical, SK 40 A = 300, Spigot Ø d1: 27mm**

**Order data**

Order number	301137 27
GTIN	4045197926852
Item class	31A

**Description**
**Version:**

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- With RFID / Balluffchip bore.
- Larger collar contact face.

**Vibration damped version, arbor with vibration-damping core.**

**Advantage:**

Significantly lower tendency to vibrate! Considerable increase in feed rate!

**Supplied with:**

Cutter lock screw and drive dog.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

**Note:**

Further sizes on request.

**Technical description**

Milling mandrel length L <sub>4</sub>	21 mm
Ø D <sub>2</sub>	58 mm
Spigot Ø d <sub>1</sub>	27 mm
Overhang dimension A	300 mm
Clamping Ø D <sub>1</sub>	27 mm
Adapter	SK 40 A = 300

Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor