

**Garant**
**eco screw-on toolholder, short, right-hand, Shank / insert size: 16/11mm**

**Order data**

Order number	260294 16/11
GTIN	4045197927132
Item class	21U

**Description**
**Version:**

GARANT eco system screw-on toolholder with internal coolant feed to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability. With flank face cooling.

**Note:**

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. 319001 – 319886 or for shank length < 125 mm plus No. 317900.

Through-coolant: yes

ISO code toolholder: SDJCR/L 1616X11

suitable indexable insert: DC.. 11T3..

Functional width L<sub>4</sub>: 20 mm

Head length L<sub>1</sub>: 29 mm

Overall length L: 74 mm

Pack of insert screws: 269023 3

**Technical description**

Shim screw	269013 1
Overall length L	74 mm
ISO code toolholder	SDJCR/L 1616X11
Shank size	16 mm

Insert size	11 mm
Shim	269007 1
suitable indexable insert	DC.. 11T3..
Pack of insert screws	269023 3
Functional width L <sub>4</sub>	20 mm
Head length L <sub>1</sub>	29 mm
Series	Eco
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500