

**HALDER****Single taper clamping jaw flat, Thread M: M16****Order data**

Order number	370022 M16
GTIN	4030618237709
Item class	37K

**Description****Application:**

Turning the clamping screw moves the two clamping jaws outwards and presses the workpieces against a fixed stop.

**Material:**

Base of tool steel, hardened, bright finish. Base of tool steel, hardened, burnished and ground.

**Note:**

Installation in a tapped hole or using a nut on T-slots. Horizontal or vertical multiple clamping can be performed.

**Technical description**

Thread M	M16
B <sub>1</sub>	56 mm
Length	57 - 64 mm
Clamping force	50 kN
maximum tightening torque	210 Nm
Height H	34 mm

Type of product

Wedge clamp