

**KÄRCHER****Industrial vacuum cleaner, Manufacturer's designation: IVR-L40****Order data**

Order number	078522 IVR-L40
GTIN	4054278459684
Item class	07D

**Description****Version:**

Industrial vacuum cleaner suitable for vacuuming up and separating **coolants, lubricating emulsions, water or oil with solids (e.g. metal chips)**.

- **Compact design and robust materials for the best movement characteristics.**
- **Maximum flexibility in use and long working life for the oil-resistant power cable.**
- **Suction is applied via a 360° rotatable hose connection on the suction head.**

1-motor 1.2 kW industrial vacuum cleaner **40 litre tank**.

**Supplied with:**

With tilting chassis, and drain hose with level indicator. **Without accessories. Suitable accessories can be found under No. 078524, 078529 and 078533.**

**Note:**

A version with 100-litre stainless steel container can be found under No. 078522 size IVR-L100DP in our eShop.

**Technical description**

Length	711 mm
Air flow volume	59 l/s

Container volume	40 l
Operating noise	71 dB(A)
Width	523 mm
Manufacturer's designation	IVR-L 40/12-1
Dust class – vacuum cleaner	L
Dust class – vacuum cleaner	L
Connection width	DN50 mm
Power consumption	1200 W
Cable length	6 m
Height	960 mm
Weight	36 kg
Vacuum	230 mbar
Number of turbines	1
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

## Accessories

Set for vacuuming chips and liquids Connection width DN40	078529 DN40
Swarf basket for the industrial vacuum cleaner Volume 20 l	078524 20
Reducing adaptor Connection width DN40	078533 DN40