

Garant**CNMM 160624, Type: HB7020****Order data**

Order number	250462 HB7020
GTIN	4045197948441
Item class	21G

Description

CNMM 160624 HB7020 Grade: HB7020
Chip breaker: SR
Cutting depth a_p : 2 - 10 mm
Feed f : 0.4 - 1.2 mm/rev.
Cutting speed v_c main application: 100 - 300 m/min

Technical description

Cutting speed v_c main application	100 - 300 m/min
Finishing/roughing assignment	Roughing
Cutting conditions	slightly interrupted
Corner radius	2.4 mm
Main application	P
Feed f	0.4 - 1.2 mm/rev.
Tool material	Carbide

Chip breaker	SR
Grade	HB7020
Cutting depth a_p	2 - 10 mm
ISO code indexable insert	CNMM 160624
Number of changes/inserts	4
Type of product	Indexable insert for turning