

Garant
CNMM 120416, Type: HB7035-1

Order data

Order number	250455 HB7035-1
GTIN	4045197948427
Item class	21G

Description

CNMM 120416 HB7035-1 Grade: HB7035-1
 Chip breaker: SR
 Cutting depth a_p : 2 - 10 mm
 Feed f : 0.4 - 1.2 mm/rev.
 Cutting speed v_c main application: 90 - 260 m/min

Technical description

Tool material	Carbide
Cutting depth a_p	2 - 10 mm
Feed f	0.4 - 1.2 mm/rev.
Cutting speed v_c main application	90 - 260 m/min
Corner radius	1.6 mm
Finishing/roughing assignment	Roughing
Main application	P

Cutting conditions	heavily interrupted
Chip breaker	SR
Grade	HB7035-1
ISO code indexable insert	CNMM 120416
Number of changes/inserts	4
Type of product	Indexable insert for turning