


Garant**SCMT 120408, Grade: HB7020**

Order data

Order number	260750 HB7020
GTIN	4045197948502
Item class	21G

Description

SCMT 120408 HB7020 Corner radius: 0.8 mm

Grade: HB7020

Chip breaker: SS

Cutting depth a_p : 0.2 - 1.5 mmFeed f : 0.05 - 0.2 mm/rev.Cutting speed v_c main application: 150 - 400 m/min

Technical description

Chip breaker	SS
Cutting conditions	slightly interrupted
Grade	HB7020
Finishing/roughing assignment	Finishing
Tool material	Carbide
Corner radius	0.8 mm
Feed f	0.05 - 0.2 mm/rev.

Main application	P
Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	150 - 400 m/min
ISO code indexable insert	SCMT 120408
Number of changes/inserts	4
Type of product	Indexable insert for turning