

Garant**DNMG 150404, Type: HB7010-1**

Order data

Order number	250670 HB7010-1
GTIN	4045197948908
Item class	21G

Description

DNMG 150404 HB7010-1 Grade: HB7010-1
Chip breaker: SS
Cutting depth a_p : 0.3 - 2 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 150 - 500 m/min

Technical description

Tool material	Carbide
Cutting conditions	continuous
Feed f	0.1 - 0.4 mm/rev.
Cutting speed v_c main application	150 - 500 m/min
Corner radius	0.4 mm
Cutting depth a_p	0.3 - 2 mm
Grade	HB7010-1

Main application	P
Finishing/roughing assignment	Finishing
Chip breaker	SS
Coating	coated
ISO code indexable insert	DNMG 150404
Number of changes/inserts	4
Type of product	Indexable insert for turning