

**WEKEM®****Liquid metal paste 2×250 g, Contents: 500g**

## Order data

Order number	083382 500
GTIN	4260205366004
Item class	04L

## Description

**Version:**

2-component epoxy putty for steel with high pressure resistance. Outstanding resistance to aggressive chemicals. Highly suitable for machining after curing.

**Application:**

For repairs to castings, for repairing cracks in housings and machine tool components and for building up worn metal parts.

**Note:**

Not available in all countries. Express delivery not possible.

## Technical description

Labelling of hazardous substances	GHS07: Exclamation mark
Labelling of hazardous substances	GHS09 harmful to the environment
Tensile shear strength	25 N/mm <sup>2</sup>
Manufacturer's designation	WS-362-500
Dynamic viscosity	750000 mPas
Suitable for application area	Repairs
Shape	Paste
Suitable for material	Aluminium
Suitable for material	wood

Suitable for material	Stainless steel
Suitable for material	Concrete
Suitable for material	Cast iron
Suitable for material	Metal
Hardness according to Shore A	68
Capacity	500 g
UN number	UN3082
Colour	grey
Working life after date of manufacture	12 mo
Storage temperature	10 °C
Characteristics	can be re-closed
hazardous goods class	9
Operating temperature range	-35 °C
Chemical basis	Epoxy resin
Density	1.8 g/cm <sup>3</sup>
Functional strength to	15 min
Touch dry after	4 - 6 min
Type of product	Two-component adhesive