


Garant
WN.G 060408, Grade: HU7305


Order data

Order number	252064 HU7305
GTIN	4045197927736
Item class	21G

Description

WN.G 060408 HU7305 Grade: HU7305

Chip breaker: AM

Tolerance: G

Cutting depth a_p : 0.5 - 5 mm

Feed f : 0.1 - 0.6 mm/rev.

Cutting speed v_c main application: 400 - 600 m/min

Technical description

Chip breaker	AM
Feed f	0.1 - 0.6 mm/rev.
Main application	N
Cutting conditions	slightly interrupted
Corner radius	0.8 mm
Cutting depth a_p	0.5 - 5 mm
Grade	HU7305

Cutting speed v_c main application	400 - 600 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	WNGG 060408
Number of changes/inserts	6
Tolerance	G
Type of product	Indexable insert for turning