

**Garant**
**DNMG 150404, Type: HB7010-1**


### Order data

Order number	250767 HB7010-1
GTIN	4045197949073
Item class	21G

### Description

DNMG 150404 HB7010-1 Grade: HB7010-1  
 Chip breaker: SM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 5 mm  
 Feed  $f$ : 0.2 - 0.5 mm/rev.  
 Cutting speed  $v_c$  main application: 120 - 440 m/min

### Technical description

Cutting conditions	continuous
Corner radius	0.4 mm
Tool material	Carbide
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Main application	P
Cutting speed $v_c$ main application	120 - 440 m/min

Chip breaker	SM
Feed f	0.2 - 0.5 mm/rev.
Grade	HB7010-1
Cutting depth $a_p$	0.5 - 5 mm
Coating	coated
ISO code indexable insert	DNMG 150404
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning