

Garant**DNMG 150408, Type: HB7035-1**

Order data

Order number	250768 HB7035-1
GTIN	4045197949134
Item class	21G

Description

DNMG 150408 HB7035-1 Grade: HB7035-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 5 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 100 - 320 m/min

Technical description

Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.5 - 5 mm
Cutting speed v_c main application	100 - 320 m/min
Tool material	Carbide
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Cutting conditions	heavily interrupted

Chip breaker	SM
Grade	HB7035-1
Main application	P
Corner radius	0.8 mm
Coating	coated
ISO code indexable insert	DNMG 150408
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning