

Garant
CNMG 160612, Grade: HB7120-1


Order data

Order number	250170 HB7120-1
GTIN	4045197927491
Item class	21G

Description

CNMG 160612 HB7120-1 Grade: HB7120-1
 Chip breaker: VM
 Tolerance: M
 Cutting depth a_p : 0.5 - 4 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 80 - 260 m/min

Technical description

Grade	HB7120-1
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Cutting conditions	continuous
Cutting depth a_p	0.5 - 4 mm
Cutting speed v_c main application	80 - 260 m/min

Corner radius	1.2 mm
Chip breaker	VM
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	CNMG 160612
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning