

**Garant****Positioning clamping pin, Ød1×length l1: 16X30mm**

## Order data

|              |               |
|--------------|---------------|
| Order number | 370105 16X30  |
| GTIN         | 4045197943798 |
| Item class   | 31E           |

## Description

### Advantage:

- Thanks to the pre-loaded spring, there is no overloading on the internal mechanism, which is thus wear resistant.
- Vibration-damping.
- Self-locking, does not work loose due to vibration.
- High repetition accuracy  $\pm 0.03$  mm.
- Low installed height.
- Easy to use.

### Application:

For quick clamping, fixing, adjusting, exchanging and securing of workpieces, plates, jigs etc.

### Material:

Through-hardened steel, burnished

## Technical description

|                       |       |
|-----------------------|-------|
| Width across flats 2  | 6 mm  |
| Length l <sub>3</sub> | 10 mm |

|                                |                |
|--------------------------------|----------------|
| Width across flats 1           | 30 mm          |
| Holding force                  | 5 kN           |
| Length $l_2$                   | 13.6 mm        |
| for clamping plates $\pm 0.05$ | 25 mm          |
| Type of product                | Clamping studs |