

Garant**CNMG 120416, Grade: HB7140-1**

Order data

Order number	250328 HB7140-1
GTIN	4045197927989
Item class	21G

Description

CNMG 120416 HB7140-1 Grade: HB7140-1
Chip breaker: VG
Cutting depth a_p : 1.5 - 6 mm
Feed f : 0.25 - 0.6 mm/rev.
Cutting speed v_c main application: 50 - 210 m/min

Technical description

Main application	M
Corner radius	1.6 mm
Feed f	0.25 - 0.6 mm/rev.
Cutting conditions	slightly interrupted
Chip breaker	VG
Cutting speed v_c main application	50 - 210 m/min
Grade	HB7140-1

Cutting depth a_p	1.5 - 6 mm
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	CNMG 120416
Number of changes/inserts	4
Type of product	Indexable insert for turning