



## Softcut®45° high-performance indexable face mill, with bore, Ø D / number of effective cutting edges Z: 100/10\_ mm

### Order data

Order number	213555 100/10_
GTIN	4045197953032
Item class	210

### Description

#### Version:

High number of cutting edges for very high productivity. Positive rake for soft cut and low power consumption. Individual tool geometry ensures very smooth cutting.

#### Note:

Use GARANT torque screwdriver TQ No. **211750 3.0** with bit No. **674252 15IP**.

Setting angle  $\kappa$ : 45 degrees

Spacing of the milling cutter's cutting edges: unequal spacing

Through-coolant: ja

Machining strategy: MTC

Tool exchange: PowerCard

### Technical description

Setting angle $\kappa$	degrees
Machining strategy	MTC
Shank type	with bore
Milling application	
Setting angle $\kappa$	degrees
Milling head suitable for insert shape	
Spacing of the cutters	unequal spacing
Through-coolant	yes
Setting angle $\kappa$	45 degrees
Tool exchange	PowerCard

Norm



Type of product

