

Garant
SNMG 190612, Grade: HB7120-1


Order data

Order number	251236 HB7120-1
GTIN	4045197928191
Item class	21G

Description

SNMG 190612 HB7120-1 Corner radius: 1.2 mm
 Grade: HB7120-1
 Chip breaker: VM
 Cutting depth a_p : 0.5 - 4 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 80 - 260 m/min

Technical description

Grade	HB7120-1
Cutting depth a_p	0.5 - 4 mm
Corner radius	1.2 mm
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Chip breaker	VM
Cutting conditions	continuous

Cutting speed v_c main application	80 - 260 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 190612
Number of changes/inserts	8
Type of product	Indexable insert for turning